Home My Account Sh

High Performance Precision Tools and Optical Inspection Systems for Industrial, Scientific and Research Applications

**Catalogs & Sales Info** 

All Products Listing

Find A Distributor

Find A Sales Rep



Tuesday, January 27th, 2009

Come and see Aven at MDM West, February 10-12, 2009 at the Anah

## Infinity 2 CCD Color Camera 3.3 Megapixel



larger image

Lumenera's INFINITY2-3 digital CCD color camera offers excellent sensitivity and high resolution. This is an ideal camera for brightfield, darkfield, and DIC imaging applications where higher resolution archiving and a wide dynamic range are routinely required. With 2080 x 1536 resolution and on-board processing, the INFINITY2-3 delivers outstanding image quality for a wide variety of scientific applications.

Live video preview provides for real-time focus while auto exposure and auto white balance efficiently captures your optimal image. The INFINITY2-3 is fully supported by Lumenera's INFINITY CAPTURE and INFINITY ANALYZE software. An intuitive user application provides camera controls while full integration to popular third-party imaging applications is available through our TWAIN drivers. The USB 2.0 digital interface ensures a simple

plug-and-play installation – and one standard cable minimizes camera clutter. No framegrabber required. The INFINITY2-3 camera is supported by an experienced team of technical support and imaging experts. We understand your imaging needs and are here to help you get the most out of your camera.

## **CAMERA SENSOR**

Image Sensor 1/1.8" Interline Sony ICX262 3.3 megapixel color progressive scan CCD sensor

Effective Pixels 2080 x 1536, 3.45µm square pixels

Frame Rate 5 fps at full resolution, higher fps with binning and ROI

Digital Output 8 and 12-bit Read Noise 12 e- rms

Readout Frequency 22.5 MHZ

Dimensions 2.25 x 3.85 x 1.56 inches (enclosed)

## **CAMERA CONTROLS**

Integration Time 1/1000 to 16 sec.

Shutter Interlaced

ROI User Selectable through mouse click and drag

Auto Exposure Automatic / Manual White Balance Automatic / Manual

Gain Programmable / 1 to 10x optimizable

Interface Connector Standard USB 2.0 high-speed interface

Dimensions (L x W x H)  $3.85 \times 2.00 \times 2.75$  inches

Lens Mount C-Mount lens adapter Binning Options 2x2, 3x3, 4x4

Mass ~300 g

Power Requirement USB 2.0 bus power, or external 5VDC - 500 mA

Power Consumption ~2.5Watts

Operating Temperature 0° C to +50° C

Operating Humidity 5%-95%, Non-condensing

## **Downloadable Documents**

Infinity Caputre & Analyze

Model: 26100-222 Shipping Weight: 1.5lbs

Add to Cart: 1

Add to Cart

Copyright © 2008 Aven, Inc. 4595 Platt Road Ann Arbor, MI 48104 734-973-0099 sa